

## SOLVING VENTILATION CHALLENGES

**New!**

Greenheck's updated Vari-Green<sup>®</sup> Constant Pressure Control now has more options and features to provide you with greater flexibility.

### Features

- Dedicated airflow control mode
- 2-line, backlit display
- More inputs/outputs
- Pressure range of +/- 1.0 inch wg
- NEMA-4 enclosure on all components

### More Options

- Two versions—  
Integral and Remote Pressure Transducer
- Integral Pressure Transducer version maintains the compact form factor of the previous "indoor" control
- Remote Pressure Transducer version provides the installation flexibility of the previous "outdoor" control by allowing the Pressure Transducer to be mounted remotely

### Inputs/Outputs

- Remote Override Input (digital, dry contact)
- Remote Setpoint Input (analog, 0-10V)
- Fan Speed Output (analog, 0-10V)
- Pressure/Airflow Reference Output (analog, 0-10V)
- Relay Output (digital, 0.5A rating)



*Control with Integral Transducer*



*Control with Remote Transducer*



*Remote Transducer*



### Airflow Measuring Station (AMS)

Now available — Accurately measure and maintain constant airflow with the AMS and Constant Airflow Control. Perfect for sensitive airflow installations or poor duct conditions where a pitot tube measurement is unacceptable.