

The toggle switches are AC rated up to 20 amps, single pole, with a slow-make, slow-break contact mechanism.

Specifications

- Certifications: UL, CSA
- Dielectric Strength: 1,000V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Phenolic
- Actuator Material: Brass/Nickel Plate
- Bushing Material: Brass/Nickel Plate

