



SKU
312409

Job Name:
Mark:
Submitted By:
Date: 04/05/2026

Motor, Large Frame, 0402SDSR41B-P, 40 HP, 3 Phase, Product # 312409

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
40 HP	3600	460	60	3	47
40 HP	3600	230	60	3	94

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	VN
Explosion Proof	No	Frame Size	324TS
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Freight

Dimensions

Shaft Diameter	1.875 in	Weight	598 lbs
-----------------------	----------	---------------	---------