



SKU
312361

Job Name:
Mark:
Submitted By:
Date: 04/22/2026

Vari-Green Motor, F2248B4177 (VG), 0.75HP, 2200RPM, 110/115V, 50/60HZ, 1PH, Product # 312361



Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.75 HP	2200	115	60	1	11.3
0.75 HP	2200	110	50	1	11.3

Specifications

Base Type	Resilient Base	Country of Origin (Primary)	US
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Housing Material	NA
Motor Enclosure	n/a	Motor Insulation	B
Motor Phase	1	Motor Type	BrushlessDC
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Parcel
Thermal Protection	AutoOverload		

Dimensions

Weight 16 lbs

California Residents

⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov