This cut sheet was generated from Greenheck Shop Online and is for the product SKU referenced below. Cut sheets for accessories or ancillary products must be printed separately.

GREENHECK Shop Online

SKU
304240

Job Name:
Mark:
Submitted By:
Date: 11/17/2026

Motor, 048S17D2053, 0.167HP, 1800 RPM, 115V, 60Hz, 1Ph, Product # 304240

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.167 HP	1800	115	60	1	3.6

Specifications

Base Type	Resilient Base	**Country of Origin (Primary)**	MX
Explosion Proof	No	**Frame Size**	48
Frame Type	n/a	**Hertz**	60
Housing Material	Rolled Steel	**HP**	1/6
Motor Enclosure	Open Drip Proof	**Motor Insulation**	B
Motor Phase	1	**Motor Type**	NEMA
NEMA Frame Size	48	**Nominal Efficiency**	56.5
Return Eligibility	Non-returnable, customized, or special-order item	**RPM**	1800
Service Factor	1.35	**Shipping Type**	Parcel
Thermal Protection	AutoOverload	**Voltage**	115

Dimensions

Shaft Diameter	0.5 in	**Weight**	12 lbs

California Residents

⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov