



SKU  
300219

Job Name:  
Mark:  
Submitted By:  
Date: 04/20/2026

## Motor, 110027, 0.5 HP, 3 Phase, Product # 300219

### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.5 HP	1200	208	60	3	2.2
0.5 HP	1200	460	60	3	1.1
0.5 HP	1200	230	60	3	2.8

### Specifications

<b>Base Type</b>	Rigid Base	<b>Country of Origin (Primary)</b>	US
<b>Explosion Proof</b>	No	<b>Frame Size</b>	56
<b>Frame Type</b>	n/a	<b>Housing Material</b>	NA
<b>Motor Enclosure</b>	Open Drip Proof	<b>Motor Insulation</b>	B
<b>Motor Phase</b>	3	<b>Motor Type</b>	NEMA
<b>Return Eligibility</b>	Non-returnable, customized, or special-order item	<b>Shipping Type</b>	Parcel

### Dimensions

<b>Shaft Diameter</b>	0.625 in	<b>Weight</b>	26 lbs
-----------------------	----------	---------------	--------

### California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)