

SKU 300494

Job Name: Mark: Submitted By: Date: 06/30/2025

# Motor, L3500, 0.25HP, 1200 RPM, 115/230V, 60Hz, 1Ph, Product # 300494

## **Performance Characteristics**

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.25 HP	1200	230	60	1	3.4
0.25 HP	1200	115	60	1	6.8

## **Specifications**

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	56
Frame Type	n/a	Housing Material	NA
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	В
Motor Phase	1	Motor Type	NEMA
Shipping Type	Parcel		

#### **Dimensions**

Shaft Diameter Weight 0.625 in 30 lbs

## California Residents



# **⚠** WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov