



SKU
308162

Job Name:
Mark:
Submitted By:
Date: 04/05/2026

Motor, 35E355T214G1, 0.75 HP, 1 Phase, Product # 308162

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.75 HP	3600	208	60	1	6.1

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	Yes	Frame Size	56
Frame Type	n/a	Housing Material	NA
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	B
Motor Phase	1	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Parcel
Thermal Protection	AutoOverload		

Dimensions

Shaft Diameter	0.625 in	Weight	40 lbs
-----------------------	----------	---------------	--------