



SKU
317855VA

Job Name:
Mark:
Submitted By:
Date: 07/04/2025

Motor, 449T, 449Tffc6088 Mod, Product # 317855VA

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
200 HP	1200	460	60	3	228

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	CN
Explosion Proof	No	Frame Size	449T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Air Over	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight		

Dimensions

Shaft Diameter	3.375 in	Weight	3050 lbs
----------------	----------	--------	----------