



SKU
319358VA

Job Name:
Mark:
Submitted By:
Date: 08/02/2025

Motor, 184T, 184Ttn16008, Product # 319358VA

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
5 HP	3600	460	60	3	5.9

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	184T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Air Over	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight		

Dimensions

Shaft Diameter	1.125 in	Weight	112 lbs
----------------	----------	--------	---------