This cut sheet was generated from Greenheck Shop Online and is for the product SKU referenced below. Cut sheets for accessories or ancillary products must be printed separate



SKU SAF-110-7X-3-QD-DR1 Job Name: Mark: Submitted By: Date: 07/16/2025

Centrifugal Supply Fan, Product # SAF-110-7X-3-QD-DR1, 1549-2581 CFM




Model SAF is a filtered supply fan designed to provide non-tempered make-up air to commercial or industrial buildings, including commercial kitchen applications. Fresh outdoor air is supplied to replace air lost through hood exhaust or general building ventilation.

- 30 x 30 inch base with prepunched mounting holes for easy attachment to roof curb
- Permanent washable aluminum filters allow for many years of reliable use
- 16.5 x 16.5 inch recommended roof opening


Certifications

AMCA Sound & Air UL/cUL 705



А	В	С	D	Е	F	G	Н
25 in	22 in	21.062 5 in	1.5 in	30 in	30 in	11.562 5 in	13.375 in

Performance Characteristics



Construction Features

Housing Material	Galvanized Steel			
Drive Type	Belt Drive			
Impeller Type	Forward curved wheel			
Impeller Material	Aluminum			
Includes	Access Panels Unassembled drive package Washable, aluminum 1-inch filters			
Certifications	AMCA Sound & Air UL/cUL 705			
Drive Package Description	Motor and drives shipped loose			
Required Accessory	Roof curb for new roof installations			

Motor Information

Motor Insulation	В			
Motor Phase	3			
Motor Type	NEMA			
Service Factor	1.25			
Voltage	208-230/460			
HP	3/4			
Hertz	60			
Motor Enclosure				
	Open Drip Proof			
RPM	1800			
RPM Thermal Protection				
	1800			

Air and Sound Performance

Motor HP	Max BHP	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25	0.375	0.5	0.625
3/4	0.76	910	730	CFM	2,581	2,416	2,229	2,044	1,830	1,549
				Sones	20	18.6	17.2	15.5	13.8	12.7

California Residents

▲ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov