This cut sheet was generated from Greenheck Shop Online and is for the product SKU referenced below. Cut sheets for accessories or ancillary products must be printed separate



SKU SAF-110-5X-3-QD-DR1 Job Name: Mark: Submitted By: Date: 07/16/2025

Centrifugal Supply Fan, Product # SAF-110-5X-3-QD-DR1, 1280-1815 CFM



Model SAF is a filtered supply fan designed to provide non-tempered make-up air to commercial or industrial buildings, including commercial kitchen applications. Fresh outdoor air is supplied to replace air lost through hood exhaust or general building ventilation.

- 30 x 30 inch base with prepunched mounting holes for easy attachment to roof curb
- Permanent washable aluminum filters allow for many years of reliable use
- 16.5 x 16.5 inch recommended roof opening

Certifications

AMCA Sound & Air UL/cUL 705



А	В	С	D	Е	F	G	Н
25 in	22 in	21.062 5 in	1.5 in	30 in	30 in	11.562 5 in	13.375 in

Performance Characteristics



Construction Features

Housing Material	Galvanized Steel		
Drive Type	Belt Drive		
Impeller Type	Forward curved wheel		
Impeller Material	Aluminum		
Includes	Access Panels Unassembled drive package Washable, aluminum 1-inch filters		
Certifications	AMCA Sound & Air UL/cUL 705		
Drive Package Description	Motor and drives shipped loose		
Required Accessory	Roof curb for new roof installations		

Motor Information

Motor Insulation	F
Motor Phase	3
Motor Type	NEMA
Voltage	208-230/460
Hertz	60
Motor Enclosure	Open Drip Proof
Thermal Protection	Thermostat

Air and Sound Performance

Motor HP	Max BHP	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25
1/2	0.26	640	540	CFM	1,815	1,565	1,280
				Sones	14	12.4	11.1

California Residents



This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov