


SKU SP-AP0511W Job Name: Mark: Submitted By: Date: 06/27/2025

Bathroom Exhaust Fan, Product # SP-AP0511W, 30-110 CFM



Model SP-AP features a virtually silent electronically commutated (EC) motor with three built-in, high-speed airflow settings (50, 80 or 110 cfm) and a handful of plug and play sensors available as add-ons.

- ENERGY STAR rated
- Virtually silent EC motor with 3 high speeds (50-80-110 CFM)
- Constant CFM technology
- Plug and play sensors available
- Universal 4", 5" or 6" duct connector
- Easy installation bracket
- Two speed capable with integral time delay




Certifications

ETL

Home Ventilating Institute (HVI)

Performance Characteristics



Construction Features

Drive Type	Direct Drive				
Includes	Backdraft damper Mounting brackets				
Certifications	ETL Home Ventilating Institute (HVI)				
Speed Controllable	Yes				
Motor Information					

Voltage	115
_	

Motor Included Yes

Air and Sound Performance

Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.1	0.125	0.25	0.375	0.5	0.625
16.5	820	820	CFM	50	50	50	50	50	50	50
			Sones	<0.3	<0.3	<0.3	0.6	1.5	2.5	3
18.1	831	831	CFM	80	80	80	80	80	80	60
			Sones	< 0.3	<0.3	<0.3	0.8	1.4	2	3
20.1	861	861	CFM	110	110	110	110	110	105	58
			Sones	0.4	0.4	0.5	0.8	1.3	2	3

California Residents



⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov