



SKU
301244

Job Name:
Mark:
Submitted By:
Date: 04/05/2026

Motor, 145TTDR5701, 0.3|1 HP, 3 Phase, Product # 301244

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
1 HP	1800	460	60	3	1.5
0.3 HP	900	460	60	3	0.75

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	MX
Explosion Proof	No	Frame Size	145T
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	Open Drip Proof	Motor Insulation	B
Motor Phase	3	Motor Type	NEMA
Return Eligibility	Returnable within 60 days of shipment	Shipping Type	Parcel

Dimensions

Shaft Diameter	0.875 in	Weight	44 lbs
----------------	----------	--------	--------

California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov