

SKU
300124Job Name:
Mark:
Submitted By:
Date: 10/14/2025

Motor, 048C17D2042, 0.25 HP, 1 Phase, Product # 300124



Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.25 HP	1800	230	60	1	2.6
0.25 HP	1800	208	60	1	2.8
0.25 HP	1800	115	60	1	5.2

Specifications

Base Type	Resilient Base	Country of Origin (Primary)	MX
Explosion Proof	No	Frame Size	48
Frame Type	n/a	Hertz	60
Housing Material	Rolled Steel	HP	1/4
Motor Enclosure	Open Drip Proof	Motor Insulation	B
Motor Phase	1	Motor Type	NEMA
NEMA Frame Size	48	Nominal Efficiency	75
RPM	1800	Service Factor	1.35
Shipping Type	Parcel	Thermal Protection	AutoOverload
Voltage	115 208 230	Watts	0.25

Dimensions

Shaft Diameter	0.5 in	Weight	15 lbs
----------------	--------	--------	--------

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov