



SKU  
311510

Job Name:  
Mark:  
Submitted By:  
Date: 08/07/2025

## Motor, D0824B4087, 198|218.7 Watts, 1350|1625 RPM, 220-240//230V, 50/60Hz, 1Ph, Product # 311510



### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
198 W	1625	230	50	1	2.2
218.7 W	1350	220	60	1	2
218.7 W	1625	230	60	1	2
198 W	1625	240	50	1	2.2
218.7 W	1350	240	60	1	2
218.7 W	1350	230	60	1	2
218.7 W	1625	220	60	1	2
198 W	1350	240	50	1	2.2
218.7 W	1625	240	60	1	2
198 W	1350	230	50	1	2.2
198 W	1350	220	50	1	2.2
198 W	1625	220	50	1	2.2

### Specifications

Base Type	Resilient Base	Country of Origin (Primary)	US
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Housing Material	NA
Motor Enclosure	n/a	Motor Insulation	B
Motor Phase	1	Motor Type	PSC
Shipping Type	Parcel	Thermal Protection	AutoOverload

### Dimensions

Weight 9.52 lbs

### California Residents

#### WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)