This cut sheet was generated from Greenheck Shop Online and is for the product SKU referenced below. Cut sheets for accessories or ancillary products must be printed separately.

GREENHECK Shop Online

SKU
306486

Job Name:
Mark:
Submitted By:
Date: 11/18/2026

Motor, 4Yu28-B, 0.5HP, 1800 RPM, 115/230V, 60Hz, 1Ph, Product # 306486

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.5 HP	1800	230	60	1	3
0.5 HP	1800	115	60	1	6

Specifications

Base Type	Rigid Base	**Bearing Type**	Ball
Country of Origin (Primary)	MX	**Explosion Proof**	No
Frame Size	48	**Frame Type**	n/a
Hertz	60	**Housing Material**	Rolled Steel
Motor Enclosure	Open Drip Proof	**Motor Insulation**	B
Motor Phase	1	**Motor Type**	NEMA
NEMA Frame Size	48Z	**Nominal Efficiency**	70
Return Eligibility	Non-returnable, customized, or special-order item	**RPM**	1725
Service Factor	1	**Shipping Type**	Parcel
Thermal Protection	AutoOverload	**Voltage**	115/230

Dimensions

Length	11.375 in	**Shaft Diameter**	0.5 in
Weight	20 lbs		

California Residents

⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov