

SKU 302577

Job Name: Mark: Submitted By: Date: 06/15/2025

# Motor, 7173-0259 Piedras, 29 Watts, 1400 RPM, 220/240//230V, 50/60Hz, 1Ph, Product # 302577

# **Performance Characteristics**

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
29 W	1400	230	60	1	0.7
29 W	1400	220	50	1	0.7
29 W	1400	240	60	1	0.7
29 W	1400	240	50	1	0.7
29 W	1400	230	50	1	0.7
29 W	1400	220	60	1	0.7

# **Specifications**

Base Type	Resilient Base	Country of Origin (Primary)	MX
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Housing Material	NA
Motor Enclosure	n/a	Motor Insulation	В
Motor Phase	1	Motor Type	PSC
Shipping Type	Parcel	Thermal Protection	AutoOverload

#### **Dimensions**

Weight

4.63 lbs

## California Residents



## **⚠** WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov