



SKU
308292VA

Job Name:
Mark:
Submitted By:
Date: 08/02/2025

Motor, 182T, 182Tts18504, Product # 308292VA

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
3 HP	3000	415	50	3	-

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	182T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Air Over	Motor Insulation	H
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight		

Dimensions

Shaft Diameter	1.125 in	Weight	94 lbs
----------------	----------	--------	--------