

SKU
301857Job Name:
Mark:
Submitted By:
Date: 08/03/2025

Motor, 143Tgn7076, 0.75HP, 1200 RPM, 208-230/460V, 60Hz, 3Ph, Product # 301857

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.75 HP	1200	230	60	3	3.2
0.75 HP	1200	208	60	3	3.1
0.75 HP	1200	460	60	3	1.6

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	MX
Explosion Proof	Yes	Frame Size	143T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	B
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight	Thermal Protection	Thermostat

Dimensions

Shaft Diameter	0.875 in	Weight	69 lbs
----------------	----------	--------	--------

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov