

SKU  
326984Job Name:  
Mark:  
Submitted By:  
Date: 08/02/2025

## Motor, Large Frame, A40-7267-0712, 125HP, 1800 RPM, 460V, 60Hz, 3Ph, Product # 326984

### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
125 HP	1800	460	60	3	141

### Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	405T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Open Drip Proof	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Shipping Type	Freight		

### Dimensions

Shaft Diameter	2.875 in	Weight	1326 lbs
----------------	----------	--------	----------

### California Residents

#### WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)