

SKU  
312359Job Name:  
Mark:  
Submitted By:  
Date: 07/17/2025

## Vari-Green Motor - 1/6 HP, 115V, 1725RPM , Product # 312359



### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.167 HP	1800	115	60	1	2.45
0.167 HP	1800	110	50	1	2.45

### Specifications

Base Type	Extended Thru-Bolt Mount	Country of Origin (Primary)	US
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Housing Material	NA
Motor Enclosure	n/a	Motor Insulation	B
Motor Phase	1	Motor Type	BrushlessDC
Shipping Type	Parcel	Thermal Protection	AutoOverload

### Dimensions

Weight 6 lbs

### California Residents

#### WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)