



SKU  
304932

Job Name:  
Mark:  
Submitted By:  
Date: 05/31/2026

## Motor, Large Frame, EM2334T, 20 HP, 3 Phase, Product # 304932

### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
20 HP	1800	460	60	3	24
20 HP	1800	208	60	3	52
20 HP	1800	230	60	3	48

### Specifications

<b>Base Type</b>	Rigid Base	<b>Country of Origin (Primary)</b>	US
<b>Explosion Proof</b>	No	<b>Frame Size</b>	256T
<b>Frame Type</b>	n/a	<b>Housing Material</b>	Cast Iron
<b>Motor Enclosure</b>	Totally Enclosed Fan Cooled	<b>Motor Insulation</b>	F
<b>Motor Phase</b>	3	<b>Motor Type</b>	NEMA
<b>Return Eligibility</b>	Non-returnable, customized, or special-order item	<b>Shipping Type</b>	Freight

### Dimensions

<b>Shaft Diameter</b>	1.625 in	<b>Weight</b>	286 lbs
-----------------------	----------	---------------	---------

### California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)