



SKU
300207

Job Name:
Mark:
Submitted By:
Date: 10/03/2025

Motor, RL1304A, 0.5 HP, 1 Phase, Product # 300207



Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.5 HP	1800	115	60	1	8.4
0.5 HP	1800	230	60	1	4.2
0.5 HP	1800	208	60	1	4.8

Specifications

Base Type	Resilient Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	56
Frame Type	n/a	Housing Material	NA
Motor Enclosure	Open Drip Proof	Motor Insulation	B
Motor Phase	1	Motor Type	NEMA
Shipping Type	Parcel	Thermal Protection	AutoOverload

Dimensions

Height	11 in	Length	17 in
Shaft Diameter	0.625 in	Weight	26 lbs
Width	12 in		

California Residents

⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov