


SKU SP-LP0511L Job Name: Mark: Submitted By: Date: 06/27/2025

MultiSpec SP-LP0511L 50/80/110 CFM Low-Profile Lighted Bathroom Exhaust Fan



- ENERGY STAR rated
- Virtually silent EC motor with 3 high speeds (50-80-110 CFM)
- Constant CFM technology
- 3-1/2 Inch Housing Depth the low profile is ideal for wall or ceiling installations. Easily fits in a 2x4 stud bay
- L-shaped bracket for support and ease of installation
- 3-year warranty on ECM motor and parts, excluding light
- 10W dimmable LED chip panel, 750 lumens, 3000K warm white color temperature, and Rated Life of 50,000 hours
- UL listed for tub/shower enclosure when GFCI protected



Certifications

UL/cUL 507 Home Ventilating Institute (HVI) ENERGY STAR® Certified

Performance Characteristics

No Fan Curve Available.

Construction Features

Drive Type	Direct Drive			
Impeller Type	Centrifugal Wheel			
Impeller Material	Polypropylene			
Includes	Backdraft damper			
	Mounting brackets			
	UL/cUL 507			
Certifications	Home Ventilating Institute			
	(HVI)			
	ENERGY STAR® Certified			
Speed Controllable	Yes			

Motor Information

Motor Phase	1	
Voltage	115	
Hertz	60	
Matte	22.6	

Air and Sound Performance

Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0.1	0.25	0.4	0.5
14.3 771	774	771 771	CFM	50	50	50	50
	771		Sones	>0.3	0.7	1.4	2.1
18.5 871	071	074	CFM	80	80	80	80
	871	Sones	0.7	1.2	1.8	2.3	
22.6	1000	1000	CFM	110	110	110	110
	1063	1063	Sones	1.5	2.1	2.2	2.3

California Residents



⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov