This cut sheet was generated from Greenheck Shop Online and is for the product SKU referenced below. Cut sheets for accessories or ancillary products must be printed separately.

GREENHECK Shop Online

SKU

358595

Job Name:

Mark:

Submitted By:

Date: 11/17/2026

# Motor, XL141522T, 1.5 HP, 1 Phase, Product # 358595

## Performance Characteristics

| Power | Speed | Voltage | Frequency | Phase | Full Load Amp Draw |
|---|---|---|---|---|---|
| 1.5 HP | 3600 | 230 | 60 | 1 | 8 |
| 1.5 HP | 3600 | 115 | 60 | 1 | 16 |
| 1.5 HP | 3600 | 208 | 60 | 1 | 8.5 |

## Specifications

| | | | |
|---|---|---|---|
| **Base Type** | Rigid Base | **Country of Origin (Primary)** | US |
| **Explosion Proof** | Yes | **Frame Size** | 143T |
| **Frame Type** | n/a | **Housing Material** | NA |
| **Motor Enclosure** | Totally Enclosed Fan Cooled | **Motor Insulation** | F |
| **Motor Phase** | 1 | **Motor Type** | NEMA |
| **Return Eligibility** | Non-returnable, customized, or special-order item | **Shipping Type** | Parcel |
| **Thermal Protection** | Thermostat | | |

## Dimensions

| | | | |
|---|---|---|---|
| **Shaft Diameter** | 0.875 in | **Weight** | 42 lbs |