



SKU
357885

Job Name:
Mark:
Submitted By:
Date: 05/24/2026

Motor, Large Frame, A40-7194-0771, 75 HP, 3 Phase, Product # 357885

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
75 HP	1200	575	60	3	70.2

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	405T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Freight

Dimensions

Shaft Diameter	2.875 in	Weight	1322 lbs
-----------------------	----------	---------------	----------