



SKU
SP-AP0511W-1

Job Name:
Mark:
Submitted By:
Date: 05/03/2025

Bathroom Exhaust Fan, Product # SP-AP0511W-1, 30-110 CFM



Model SP-AP features a virtually silent electronically commutated (EC) motor with three built-in, high-speed airflow settings (50, 80 or 110 cfm) and a handful of plug and play sensors available as add-ons.

- ENERGY STAR rated
- Virtually silent EC motor with 3 high speeds (50-80-110 CFM)
- Constant CFM technology
- Plug and play sensors available
- Universal 4", 5" or 6" duct connector
- Easy installation bracket
- Two speed capable with integral time delay
- Compatible with CRD-300WT, a UL263 certified Ceiling Radiation

Certifications

ETL

Home Ventilating Institute (HVI)

Performance Characteristics

No Fan Curve Available.

Construction Features

Drive Type	Direct Drive
Impeller Type	Centrifugal Wheel
Impeller Material	Polypropylene
Includes	Backdraft damper Mounting brackets
Certifications	ETL Home Ventilating Institute (HVI)
Speed Controllable	Yes

Motor Information

Voltage	115
Motor Included	Yes

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov