



SKU  
SP-LP0511L-1

Job Name:  
Mark:  
Submitted By:  
Date: 04/17/2026

## SP-LP0511L-1 50/80/110 CFM Low-Profile Lighted Bathroom Exhaust Fan



- ENERGY STAR rated
- Virtually silent EC motor with 3 high speeds (50-80-110 CFM)
- Constant CFM technology
- 3-1/2 Inch Housing Depth – the low profile is ideal for wall or ceiling installations. Easily fits in a 2x4 stud bay
- L-shaped bracket for support and ease of installation
- 10W dimmable LED chip panel, 750 lumens, 3000K warm white color temperature, and Rated Life of 50,000 hours
- UL listed for tub/shower enclosure when GFCI protected
- 3-year warranty on EC motor and parts, excluding light

### Certifications

UL 507  
Home Ventilating Institute (HVI)  
ENERGY STAR® Certified

### Performance Characteristics

No Fan Curve Available.

### Construction Features

Drive Type	Direct Drive
Impeller Type	Centrifugal Wheel
Impeller Material	Polypropylene
Includes	Backdraft damper Mounting brackets
Certifications	UL 507 Home Ventilating Institute (HVI) ENERGY STAR® Certified
Speed Controllable	Yes

### Motor Information

Motor Phase	1
Voltage	115
Hertz	60
Motor Included	Yes

### California Residents

**⚠ WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)