



SKU
SP-LP0511L-1

Job Name:
Mark:
Submitted By:
Date: 06/27/2025

SP-LP0511L-1 50/80/110 CFM Low-Profile Lighted Bathroom Exhaust Fan



- ENERGY STAR rated
- Virtually silent EC motor with 3 high speeds (50-80-110 CFM)
- Constant CFM technology
- 3-1/2 Inch Housing Depth – the low profile is ideal for wall or ceiling installations. Easily fits in a 2x4 stud bay
- L-shaped bracket for support and ease of installation
- 10W dimmable LED chip panel, 750 lumens, 3000K warm white color temperature, and Rated Life of 50,000 hours
- UL listed for tub/shower enclosure when GFCI protected
- 3-year warranty on EC motor and parts, excluding light

Certifications

UL 507
Home Ventilating Institute (HVI)
ENERGY STAR® Certified

Performance Characteristics

No Fan Curve Available.

Construction Features

Drive Type	Direct Drive
Impeller Type	Centrifugal Wheel
Impeller Material	Polypropylene
Includes	Backdraft damper Mounting brackets
Certifications	UL 507 Home Ventilating Institute (HVI) ENERGY STAR® Certified
Speed Controllable	Yes

Motor Information

Motor Phase	1
Voltage	115
Hertz	60
Motor Included	Yes

California Residents

WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov