



SKU  
1039436

Job Name:  
Mark:  
Submitted By:  
Date: 05/30/2026

## Motor, D0810B3214, 62.167 Watts, 1 Phase, Product # 1039436



### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
62.167 W	1350	115	60	1	1.42
62.167 W	1350	115	50	1	1.42

### Specifications

Base Type	No Base	Country of Origin (Primary)	US
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Housing Material	NA
Motor Enclosure	n/a	Motor Insulation	B
Motor Phase	1	Motor Type	PSC
Return Eligibility	Returnable within 60 days of shipment	Shipping Type	Parcel
Thermal Protection	Dual		

### Dimensions

Weight	6 lbs
--------	-------