



SKU  
1039949

Job Name:  
Mark:  
Submitted By:  
Date: 05/20/2026

## Motor, D0524B2511, 124.3 Watts, 1 Phase, Product # 1039949

### Performance Characteristics



Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
124.3 W	1050	115	60	1	4.9

### Specifications

Base Type	Extended Thru-Bolt Mount	Country of Origin (Primary)	US
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Housing Material	NA
Motor Enclosure	n/a	Motor Insulation	B
Motor Phase	1	Motor Type	Shaded Pole
Return Eligibility	Returnable within 60 days of shipment	Shipping Type	Parcel
Thermal Protection	Dual		

### Dimensions

Weight 8 lbs