



SKU
1039966

Job Name:
Mark:
Submitted By:
Date: 08/20/2025

Vari-Green Motor, Pre-Programmed, ZWK417B0050412, 0.0667 HP, 1800 RPM, 110-240V, 50|60 Hz, 1 Phase, Product # 1039966

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.067 HP	1800	115	50	1	1.3
0.067 HP	1800	110	50	1	1.3
0.067 HP	1800	220	50	1	0.65
0.067 HP	1800	115	60	1	1.3
0.067 HP	1800	230	60	1	0.65
0.067 HP	1800	208	60	1	0.65
0.067 HP	1800	230	50	1	0.65
0.067 HP	1800	240	50	1	0.65

Specifications

Base Type	Extended Thru-Bolt Mount	Country of Origin (Primary)	VN
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	n/a	Motor Insulation	B
Motor Phase	1	Motor Type	BrushlessDC
Shipping Type	Parcel	Thermal Protection	AutoOverload

Dimensions

Weight	4 lbs
--------	-------