This cut sheet was generated from Greenheck Shop Online and is for the product SKU referenced below. Cut sheets for accessories or ancillary products must be printed separately.

GREENHECK Shop Online

SKU

1043691

Job Name:

Mark:

Submitted By:

Date: 11/18/2026

Motor, 35E5455K919G1, 0.75 HP, 3 Phase, Product # 1043691



Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.75 HP	1800	230	60	3	2
0.75 HP	1800	460	60	3	1
0.75 HP	1800	208	60	3	2.2

Specifications

Base Type	Rigid Base	**Country of Origin (Primary)**	US
Explosion Proof	No	**Frame Size**	56
Frame Type	n/a	**Housing Material**	Rolled Steel
Motor Enclosure	Open Drip Proof	**Motor Insulation**	F
Motor Phase	3	**Motor Type**	NEMA
Return Eligibility	Returnable within 60 days of shipment	**Shipping Type**	Parcel
Thermal Protection	AutoOverload		

Dimensions

Shaft Diameter	0.625 in	**Weight**	35 lbs