


SKU SP-LP0810W Job Name: Mark: Submitted By: Date: 09/04/2025

# MultiSPEC SP-LP0810W Low-Profile Exhaust Fan with 2 Speed Whole-House Continuous Ventilation



- ENERGY STAR rated
- Constant CFM technology
- 3-1/2 Inch Housing Depth the low profile is ideal for wall or ceiling installations. Easily fits in a 2x4 stud bay
- UL listed for tub/shower enclosure when GFCI protected
- 3-year warranty on EC motor and parts, excluding light
- Virtually silent EC motor with 2 high speeds (80 and 100 CFM)
- Includes two-speed whole-house continuous ventilation (30-100 CFM range)



## Certifications

UL 507

Home Ventilating Institute (HVI) ENERGY STAR® Certified

#### **Performance Characteristics**

No Fan Curve Available.

### **Construction Features**

Drive Type	Direct Drive				
Impeller Type	Centrifugal Wheel				
Impeller Material	Polypropylene				
Includes	Backdraft damper Mounting brackets				
Certifications	UL 507 Home Ventilating Institute (HVI) ENERGY STAR® Certified				
Speed Controllable	Yes				

# **Motor Information**

Motor Phase	1	
Voltage	115	
Hertz	60	
Watts	22.7	

#### Air and Sound Performance

Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0.10	0.25	0.40	0.50	0.1	0.4	0.5
13.5 752	750	752 752	CFM	-	50	-	-	50	50	50
	752		Sones	-	0.7	-	-	>0.3	1.4	2.1
18.2 7	700	700	CFM	80	80	80	80	-	-	-
	799	799 799	Sones	0.5	1	1.5	2.5	-	-	-
18.5	000	838	CFM	-	80	-	-	80	80	80
	838		Sones	-	1.2	-	-	0.7	1.8	2.3
23.9	894	894 894	CFM	100	100	100	100	-	-	-
			Sones	0.9	1.5	2	3	-	-	-
22.7	1017	1017	CFM	-	110	-	-	110	110	110
			Sones	-	2.1	-	-	1.5	2.2	2.3

## California Residents



## **⚠** WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov