


SKU SP-LP0810WL Job Name: Mark: Submitted By: Date: 09/04/2025

MultiSPEC SP-LP0810WL Low-Profile Lighted Exhaust Fan with 2-Speed Whole-House Continuous Ventilation



- ENERGY STAR rated
- Constant CFM technology
- 3-1/2 Inch Housing Depth the low profile is ideal for wall or ceiling installations. Easily fits in a 2x4 stud bay
- UL listed for tub/shower enclosure when GFCI protected
- 3-year warranty on EC motor and parts, excluding light
- Virtually silent EC motor with 2 high speeds (80 and 100 CFM)
- Includes two-speed whole-house continuous ventilation (30-100 CFM range)



Certifications

UL/cUL 507 Home Ventilating Institute (HVI) ENERGY STAR® Certified

Performance Characteristics

No Fan Curve Available.

Construction Features

Drive Type	Direct Drive				
Impeller Type	Centrifugal Wheel				
Impeller Material	Polypropylene				
Includes	Backdraft damper Mounting brackets				
Certifications	UL/cUL 507 Home Ventilating Institute (HVI) ENERGY STAR® Certified				
Speed Controllable	Yes				

Motor Information

Motor Phase	1	
Voltage	115	
Hertz	60	
Watts	22.6	

Air and Sound Performance

Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0.1	0.25	0.4	0.5	0.10	0.40	0.50
14.3 77	774	771 771	CFM	50	50	50	50	-	-	-
	//1		Sones	>0.3	0.7	1.4	2.1	-	-	_
19.1 822	000	2 822	CFM	-	80	-	-	80	80	80
	822		Sones	-	1	-	-	0.6	1.5	2
18.5 871	074	871	CFM	80	80	80	80	-	-	-
	8/1		Sones	0.7	1.2	1.8	2.3	-	-	-
25.2 939	000	939 939	CFM	-	100	-	-	100	100	100
	939		Sones	-	1.5	-	-	1	2	2.5
22.6	1063	1063	CFM	110	110	110	110	-	-	-
			Sones	1.5	2.1	2.2	2.3	-	-	-

California Residents



⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov