



SKU  
1043776

Job Name:  
Mark:  
Submitted By:  
Date: 04/07/2026

## Vari-Green Motor, ZWK601B514024, 0.1|0.25 HP, 1 Phase, Product # 1043776

### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.25 HP	1800	230	50	1	2.5
0.25 HP	1800	110	50	1	4.3
0.167 HP	1800	208	50	1	2
0.167 HP	1800	240	50	1	1.8
0.167 HP	1800	277	50	1	1.5
0.1 HP	1800	220	50	1	1.2
0.167 HP	1800	115	60	1	3.15
0.1 HP	1800	240	60	1	1.2
0.1 HP	1800	277	50	1	1.05
0.1 HP	1800	240	50	1	1.2
0.167 HP	1800	230	60	1	1.8
0.25 HP	1800	220	60	1	2.5
0.167 HP	1800	220	60	1	1.8
0.1 HP	1800	220	60	1	1.2
0.25 HP	1800	277	50	1	2.15
0.167 HP	1800	220	50	1	1.8
0.1 HP	1800	230	60	1	1.2
0.25 HP	1800	240	50	1	2.5
0.25 HP	1800	240	60	1	2.5
0.167 HP	1800	240	60	1	1.8
0.25 HP	1800	115	60	1	4.3
0.167 HP	1800	230	50	1	1.8
0.167 HP	1800	115	50	1	3.15
0.167 HP	1800	208	60	1	2
0.25 HP	1800	220	50	1	2.5
0.25 HP	1800	208	50	1	2.8
0.25 HP	1800	277	60	1	2.15
0.1 HP	1800	115	50	1	2.1
0.1 HP	1800	230	50	1	1.2
0.1 HP	1800	277	60	1	1.05
0.25 HP	1800	230	60	1	2.5
0.25 HP	1800	115	50	1	4.3
0.1 HP	1800	208	50	1	1.35
0.1 HP	1800	208	60	1	1.35
0.167 HP	1800	277	60	1	1.5
0.25 HP	1800	208	60	1	2.8
0.1 HP	1800	115	60	1	2.1

## Specifications

---

<b>Base Type</b>	Rigid Base	<b>Country of Origin (Primary)</b>	VN
<b>Explosion Proof</b>	n/a	<b>Frame Size</b>	n/a
<b>Frame Type</b>	n/a	<b>Housing Material</b>	Rolled Steel
<b>Motor Enclosure</b>	n/a	<b>Motor Insulation</b>	B
<b>Motor Phase</b>	1	<b>Motor Type</b>	BrushlessDC
<b>Return Eligibility</b>	Non-returnable, customized, or special-order item	<b>Shipping Type</b>	Parcel
<b>Thermal Protection</b>	AutoOverload		

## Dimensions

---

<b>Height</b>	5 in	<b>Length</b>	8 in
<b>Weight</b>	10 lbs	<b>Width</b>	5 in

## California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)