



SKU
356706

Job Name:
Mark:
Submitted By:
Date: 04/03/2026

Motor, 35E362K069G1, 0.6|1 HP, 3 Phase, Product # 356706

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.6 HP	900	575	60	3	1
1 HP	1200	575	60	3	1.3

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	US
Explosion Proof	No	Frame Size	145T
Frame Type	n/a	Housing Material	Rolled Steel
Motor Enclosure	Totally Enclosed Fan Cooled	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Freight
Thermal Protection	Thermostat		

Dimensions

Shaft Diameter	0.875 in	Weight	73 lbs
-----------------------	----------	---------------	--------