This cut sheet was generated from Greenheck Shop Online and is for the product SKU referenced below. Cut sheets for accessories or ancillary products must be printed separately.

GREENHECK Shop Online

SKU

1085519

Job Name:

Mark:

Submitted By:

Date: 11/18/2026

Motor, Custom, 1.5 HP, 3 Phase, Product # 1085519

Performance Characteristics

Specifications

Base Type	Rigid Base	**Country of Origin (Primary)**	US
Explosion Proof	No	**Frame Size**	143T
Frame Type	n/a	**Housing Material**	Rolled Steel
Motor Enclosure	Totally Enclosed Fan Cooled	**Motor Insulation**	F
Motor Phase	3	**Motor Type**	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	**Shipping Type**	Freight

Dimensions

Shaft Diameter	0.625 in	**Weight**	0 lbs