

SKU SP-A110-L-QD Job Name: Mark: Submitted By: Date: 08/20/2025

Lighted Bathroom Exhaust Fan, Product # SP-A110-L-QD, 98-130 CFM




Model SP-A direct drive, ceiling mounted fan is designed to provide the lowest sounds levels for bathroom exhaust. Units feature an insulated housing, lighted grille and are ideal for residential, multi-family or hotel applications.


- Acoustic insulation absorbs sound ensuring quiet operation
- External electrical access reduces installation time
- Industry leading low sound levels
- Speed controllable
- Spring loaded aluminum backdraft damper eliminates rattling
- Designer grille included

Certifications

AMCA Air & Sound UL/cUL 507



Performance Characteristics



Construction Features

Galvanized Steel	
Direct Drive	
Centrifugal Wheel	
Polypropylene	
Backdraft damper	
Lighted grille	
Mounting brackets	
AMCA Air & Sound	
UL/cUL 507	
Yes	

Motor Information

Motor Insulation	A
Motor Phase	1
Motor Type	PSC
Service Factor	1
Voltage	115
Hertz	60
Motor Enclosure	n/a
RPM	950
Thermal Protection	AutoOverload
Nominal Efficiency	24
Watts	18.5

Air and Sound Performance

Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25
19.4 950			CFM	130	115	98
	950 760	Sones	<0.3	<0.3	0.5	



- Greenheck Fan Corporation certifies that the SP models shown herein are licensed to bear the AMCA seal.
- The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 211 and AMCA Publication 311 and comply with the requirements of the AMCA Certified Ratings Program.
- The SP models are not AMCA certified with 50 hertz motors.

California Residents



⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov