



SKU
302529

Job Name:
Mark:
Submitted By:
Date: 05/31/2026

Motor, F0412B2690, 18.8 Watts, 1 Phase, Product # 302529



Performance Characteristics

| Power | Speed | Voltage | Frequency | Phase | Full Load Amp Draw |
|--------|-------|---------|-----------|-------|--------------------|
| 18.8 W | 1300 | 115 | 60 | 1 | 1 |
| 18.8 W | 1050 | 115 | 60 | 1 | 1 |
| 18.8 W | 1550 | 115 | 60 | 1 | 1.2 |

Specifications

| | | | |
|---------------------------|---------------------------------------|------------------------------------|-------------|
| Base Type | Extended Thru-Bolt Mount | Country of Origin (Primary) | US |
| Explosion Proof | n/a | Frame Size | n/a |
| Frame Type | n/a | Housing Material | NA |
| Motor Enclosure | n/a | Motor Insulation | B |
| Motor Phase | 1 | Motor Type | Shaded Pole |
| Return Eligibility | Returnable within 60 days of shipment | Shipping Type | Parcel |
| Thermal Protection | AutoOverload | | |

Dimensions

| | | | |
|---------------|-------|---------------|-------|
| Height | 10 in | Length | 11 in |
| Weight | 4 lbs | Width | 11 in |

California Residents

⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov