



SKU
311735

Job Name:
Mark:
Submitted By:
Date: 06/12/2026

Motor, F0408B4158, 3.7|5 Watts, 690 RPM, 220-240//230V, 50/60Hz, 1Ph, Product # 311735



Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
5 W	690	230	50	1	0.41
5 W	690	220	50	1	0.41
5 W	690	240	50	1	0.41
3.7 W	690	240	60	1	0.38
3.7 W	690	220	60	1	0.38
3.7 W	690	230	60	1	0.38

Specifications

Base Type	Resilient Base	Country of Origin (Primary)	US
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Housing Material	NA
Motor Enclosure	n/a	Motor Insulation	B
Motor Phase	1	Motor Type	Shaded Pole
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Parcel
Thermal Protection	OneShot		

Dimensions

Weight 5 lbs

California Residents

⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov