

SKU SP-B110-QD Job Name: Mark: Submitted By: Date: 10/26/2025

Bathroom Exhaust Fan, Product # SP-B110-QD, 50-133 CFM




Low profile bathroom exhaust fan, Model SP-B features a forward-curved wheel for low sound and high efficiency. Units are ideal for residential, multifamily or hotel applications.


- Motion and humidity sensing grille options available
- Compact size for height restricted areas
- Integral damper prevents unwanted backdrafts
- Round standard outlet for quick, easy connections
- Speed controllable
- Designer grille included

Certifications

AMCA Air & Sound UL/cUL 507



Performance Characteristics



Construction Features

Housing Material	Galvanized Steel					
Drive Type	Direct Drive					
Impeller Type	Centrifugal Wheel					
Impeller Material	Polypropylene					
Includes	Backdraft damper Mounting brackets					
Certifications	AMCA Air & Sound UL/cUL 507					
Speed Controllable	Yes					

Motor Information

Motor Insulation	В
Motor Phase	1
Motor Type	Shaded Pole
Service Factor	1
Voltage	115
Hertz	60
Motor Enclosure	n/a
RPM	950
Thermal Protection	AutoOverload
Nominal Efficiency	12
Watts	8

Air and Sound Performance

Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25	0.375	0.5	0.625	0.75	0.875	1
80.2 950	760	CFM	133	110	97	95	94	91	85	72	50	
		Sones	1.5	1.5	2	2	2	3	3.5	4	4.5	



- Greenheck Fan Corporation certifies that the SP models shown herein are licensed to bear the AMCA seal.
- The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 211 and AMCA Publication 311 and comply with the requirements of the AMCA Certified Ratings Program.
- The SP models are not AMCA certified with 50 hertz motors.

California Residents



⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov