

SKU SP-B90-QD Job Name: Mark: Submitted By: Date: 10/16/2025

Bathroom Exhaust Fan, Product # SP-B90-QD, 57-104 CFM




Low profile bathroom exhaust fan, Model SP-B features a forward-curved wheel for low sound and high efficiency. Units are ideal for residential, multifamily or hotel applications.


- ENERGY STAR rated
- Compact size for height restricted areas
- Round standard outlet for quick, easy connections
- Integral damper prevents unwanted backdrafts
- Speed controllable
- Designer grille included

Certifications

AMCA Air & Sound UL/cUL 507



Performance Characteristics



Construction Features

Housing Material	Galvanized Steel			
Drive Type	Direct Drive			
Impeller Type	Centrifugal Wheel			
Impeller Material	Polypropylene			
Includes	Backdraft damper Mounting brackets			
Certifications	AMCA Air & Sound UL/cUL 507			
Speed Controllable	Yes			

Motor Information

Motor Insulation	В
Motor Phase	1
Motor Type	PSC
Service Factor	1
Voltage	115
Hertz	60
Motor Enclosure	n/a
RPM	900
Nominal Efficiency	20.5
Watts	5

Air and Sound Performance

	Watts	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25	0.375
				CFM	104	89	72	57
2	21.1	700 560	Sones	1	1	1.5	2	



- Greenheck Fan Corporation certifies that the SP models shown herein are licensed to bear the AMCA seal.
- The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 211 and AMCA Publication 311 and comply with the requirements of the AMCA Certified Ratings Program.
- The SP models are not AMCA certified with 50 hertz motors.

California Residents



⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov