



SKU
311736

Job Name:
Mark:
Submitted By:
Date: 06/06/2026

Motor, F0408B4157, 4.7|9 Watts, 950 RPM, 220-240//230V, 50/60Hz, 1Ph, Product # 311736



Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
9 W	950	230	50	1	-
4.7 W	950	230	60	1	-
9 W	950	240	50	1	0.63
9 W	950	220	50	1	-
4.7 W	950	220	60	1	-
4.7 W	950	240	60	1	0.51

Specifications

Base Type	Resilient Base	Country of Origin (Primary)	US
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Housing Material	NA
Motor Enclosure	n/a	Motor Insulation	B
Motor Phase	1	Motor Type	Shaded Pole
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Parcel
Thermal Protection	AutoOverload		

Dimensions

Height	4 in	Length	5 in
Weight	10 lbs	Width	4 in

California Residents

⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov