



SKU  
311377

Job Name:  
Mark:  
Submitted By:  
Date: 05/22/2026

## Vari-Green Motor - 1/4 HP, 115V, 1725RPM , Product # 311377



### Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.25 HP	1800	110	50	1	3.5
0.25 HP	1800	115	60	1	3.5

### Specifications

<b>Base Type</b>	Resilient Base	<b>Country of Origin (Primary)</b>	US
<b>Explosion Proof</b>	n/a	<b>Frame Size</b>	n/a
<b>Frame Type</b>	n/a	<b>Hertz</b>	60
<b>Housing Material</b>	NA	<b>HP</b>	1/4
<b>Motor Enclosure</b>	n/a	<b>Motor Insulation</b>	B
<b>Motor Phase</b>	1	<b>Motor Type</b>	BrushlessDC
<b>Nominal Efficiency</b>	80	<b>Return Eligibility</b>	Non-returnable, customized, or special-order item
<b>RPM</b>	1800	<b>Service Factor</b>	1
<b>Shipping Type</b>	Parcel	<b>Thermal Protection</b>	AutoOverload
<b>Voltage</b>	115		

### Dimensions

**Weight** 7 lbs

### California Residents

**⚠ WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)