



SKU
306623VA

Job Name:
Mark:
Submitted By:
Date: 04/09/2026

Motor, 60HP, 1800 RPM, 208V, 60Hz, 3Ph, Product # 306623VA

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
60 HP	1800	208	60	3	-

Specifications

Base Type	Rigid Base	Country of Origin (Primary)	CN
Explosion Proof	No	Frame Size	364T
Frame Type	n/a	Housing Material	Cast Iron
Motor Enclosure	Totally Enclosed Air Over	Motor Insulation	F
Motor Phase	3	Motor Type	NEMA
Return Eligibility	Non-returnable, customized, or special-order item	Shipping Type	Freight

Dimensions

Shaft Diameter	2.375 in	Weight	0 lbs
-----------------------	----------	---------------	-------

California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov