



SKU
327959

Job Name:
Mark:
Submitted By:
Date: 04/02/2026

Vari-Green Motor, Pre-Programmed, SP-A50-90-VG,UNADA. Product # 327959

Performance Characteristics

Power	Speed	Voltage	Frequency	Phase	Full Load Amp Draw
0.016 HP	2300	240	50	1	0.25
0.016 HP	2300	115	50	1	0.29
0.016 HP	2300	115	60	1	0.29
0.016 HP	2300	240	60	1	0.25
0.016 HP	2300	220	60	1	0.25
0.016 HP	2300	230	60	1	0.25
0.016 HP	2300	230	50	1	0.25
0.016 HP	2300	220	50	1	0.25

Specifications

Base Type	Extended Thru-Bolt Mount	Country of Origin (Primary)	TH
Explosion Proof	n/a	Frame Size	n/a
Frame Type	n/a	Hertz	60
Housing Material	NA	HP	1/60
Motor Enclosure	n/a	Motor Insulation	B
Motor Phase	1	Motor Type	BrushlessDC
Nominal Efficiency	1	Return Eligibility	Non-returnable, customized, or special-order item
RPM	2300	Service Factor	1
Shipping Type	Parcel	Thermal Protection	AutoOverload
Voltage	120 230		

Dimensions

Height	7 in	Length	7 in
Weight	1.6 lbs	Width	7 in

California Residents

 **WARNING**

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov