

SKU CUE-100-4VG119GQD

Job Name: Mark: Submitted By: Date: 04/26/2024

Centrifugal Upblast Exhaust Fan, Product # CUE-100-4VG119GQD, 411-1468 CFM



Model CUE is a direct drive exhaust fan specifically designed for roof or sidewall mounted applications discharging the air directly upward, away from the roof or wall surface. The fans feature a one piece windband continuously welded to curb cap and double studded isolators for true vibration isolation.

- 19 x 19 inch base with prepunched mounting holes for easy attachment to roof curb
- Energy-efficient, speed controllable, Vari-green® motor
- Roof or wall mountable


A B C 28.25 in 28.25 in

Certifications

AMCA Sound & Air

UL/cUL 705 Listed - Supplement SC - "Power Ventilators for Restaurant Exh. Appliances" (Formerly UL 762)

Performance Characteristics



Construction Features

Housing Material	Spun Aluminum					
Drive Type	Direct Drive					
Impeller Type	Centrifugal Wheel					
Impeller Material	Aluminum					
Includes	Motor mounted potentiometer					
Certifications	AMCA Sound & Air UL/cUL 705 Listed - Supplement SC - "Power Ventilators for Restaurant Exh. Appliances" (Formerly UL 762)					
Speed Controllable	Yes					
Required Accessory	Roof curb for new roof installations					

Motor Information

Motor Insulation	В				
Motor Phase	1				
Service Factor	1.25				
	115				
Voltage	208				
	230				
	277				
HP	1/4				
Hertz	60				
Motor Enclosure	n/a				
RPM	1800				
Thermal Protection	AutoOverload				
Nominal Efficiency	85				

Air and Sound Performance

Motor HP	Max BHP	Max Fan RPM	Min Fan RPM	Ps (in. wg)	0	0.125	0.25	0.375	0.5	0.625	0.75	0.875	1
1/4 0.29	1725	720	CFM	1,468	1,422	1,373	1,315	1,255	1,195	1,129	1,062	970	
			Sones	13.3	12.9	12.5	12	11.7	11.3	10.8	10.2	9.7	



- Greenheck Fan Corporation certifies that the model shown herein is licensed to bear the AMCA Seal. The ratings shown are based on tests and procedures performed in accordance with AMCA Publication 211 and AMCA Publication 311 and comply with the requirements of the AMCA Certified Ratings Program.
- Performance certified is for installation type A: Free inlet, Free outlet.
- Power rating (BHP/kW) does not include transmission losses.
- Performance ratings do not include the effects of appurtenances (accessories).
- The sound ratings shown are loudness values in fan sones at 5 ft. (1.5 m) in a hemispherical free field calculated per AMCA Standard 301. Values shown are for installation type A: free inlet hemispherical sone levels.

California Residents



⚠ WARNING

This product can expose you to chemicals including cadmium used in the processing of corrosion resistant metal and fasteners, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information visit www.P65Warnings.ca.gov