

Ceiling Radiation Damper Low Profile Rectangular


Application and Design

The CRD-1LP (Low Profile) has been UL tested and labeled for protection of ceiling openings in fire rated floor/ceiling assemblies with fire resistance ratings of 3 hours or less. CRD-1LP is intended to be used on applications with limited blade clearance. This product can also be applied to steel lay-in style ceiling diffusers up to 24 in. x 24 in. (610mm x 610mm) maximum size when installed with an approved thermal blanket.

Construction		Standard	Optional
Frame		Galvanized Steel*	-
Frame Type		Standard	Top, Bottom, or Top/Bottom Extension
Blades		Galvanized Steel*	-
Fusible Link Temperature		165°F (74°C)	212°F (100°C)
Blade Insulation	Under 115.46 sq. in. (74,490 sq. mm)	Not required	-
	Over 115.46 sq. in. (74,490 sq. mm)	Non-asbestos UL classified	-


* in gauges required by UL listing R13446

“UL CLASSIFIED
(see complete marking on product)”
“UL CLASSIFIED to Canadian safety standards
(see complete marking on product)”
 Standard 555C (Listing #R13446)
National Fire Protection Association:
 NFPA Standards 90A and 101
CSFM California State Fire Marshal
 Fire Damper Listing (#3225-0981:0101)
New York City MEA Listing #260-91-M



*W & H dimensions furnished approximately 1/4 in. (6mm) under size.

W & H	Minimum Size	Maximum Size
Inches	4 x 12	24 x 24
mm	101 x 305	610 x 610



Blade Extension = Nominal Height/4 - 2.375

Frame Dimensions					
Damper Model	Height (in.)	A	B	C	D
CRD-1LP Standard Frame	12 - 24	2 3/4	-	-	-
CRD-1LP B Bottom Extension	12 - 24	-	4 3/4	-	-
CRD-1LP T Top Extension	12 - 16 1/2	-	-	4 3/4	-
	16 1/2 - 20 1/4	-	-	5 3/4	-
	20 1/4 - 24	-	-	6 3/4	-
CRD-1LP BT Bottom and Top Extension	12 - 16 1/4	-	-	-	6 7/8
	16 1/2 - 20 1/4	-	-	-	7 7/8
	20 1/4 - 24	-	-	-	8 7/8

Volume Controller Option

A volume controller is used to manually set the blades at a given angle to regulate the airflow (24 in. x 24 in. [610mm x 610mm] maximum). Adjusting the cap screw will open and close the blades.

Thermal Blanket Option

Ceramic fiber or mineral wool thermal blanket available.